

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301020233](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway Rubber Hand Lamp, PAR 38 Guard, with Switch, 15.24m (50.0') 16/3 SOOW

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Portable Lighting
Series	<a href="#">130102</a>
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	<a href="#">Hand Lamps</a>
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678835493

**Physical**

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Industrial
Guard Included	Yes
Guard Type	Open End, PAR 38
Height	285.50mm (11.240")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	PAR38
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

**Material Info**

Engineering Number	119UB163
--------------------	----------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130102 Series](#)