

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030021](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Watertite Wet Location Incandescent Hand Lamp Only, 100W with Screw Release Ungrounded Vinyl Guard

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130103](#)
 NEMA Configuration N/A
 NEMA Rating NEMA 4X
 Outlet None
 Overview [Hand Lamps](#)
 Product Name Watertite
 Taxonomy Lamps and Lights
 Type Hand Lamps
 UPC 78678861293

Physical

Cord Length - Primary N/A
 Cord Length - Secondary N/A
 Depth 120.65mm (4.750")
 Duty Wet Location
 Guard Included Yes
 Guard Type Insulated, Screw Release
 Height 457.20mm (18.000")
 Length N/A
 Material - Globe Tempered Glass
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120V AC

Material Info

Engineering Number 12031



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130103 Series](#)