

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030025](#)

Status: **Active**

Overview: [Hand Lamps](#)

Description: Watertite Wet Location Incandescent Hand Lamp, 100W with Clear Poly Carbonate Globe, Screw Release Grounded Vinyl Guard, Cord Type 16/3 SOOW, Cord Length 15.24m (50.0')

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130103
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Hand Lamps
Product Name	Watertite
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678838710
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Grounded, Insulated, Screw Release
Height	457.20mm (18.000")
Length	N/A
Material - Globe	Clear Polycarbonate
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC
Material Info	
Engineering Number	1203IB163P



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130103 Series](#)