

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301030034](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Watertite Wet Location Incandescent Hand Lamp Only, 100W with Poly Carb Globe, Screw Release Insulated Guard with Reflector

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130103](#)  
 NEMA Configuration N/A  
 NEMA Rating NEMA 4X  
 Outlet None  
 Overview [Hand Lamps](#)  
 Product Name Watertite  
 Taxonomy Lamps and Lights  
 Type Hand Lamps  
 UPC 78678805739

**Physical**

Cord Length - Primary N/A  
 Cord Length - Secondary N/A  
 Depth 120.65mm (4.750")  
 Duty Wet Location  
 Guard Included Yes  
 Guard Type Insulated, Reflector, Screw Release  
 Height 457.20mm (18.000")  
 Length N/A  
 Material - Globe Clear Polycarbonate  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120V AC

**Material Info**

Engineering Number 1203PRI



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130103 Series](#)