

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030045](#)

Status: **Active**

Overview: [Hand Lamps](#)

Description: Watertite Wet Location Incandescent Hand Lamp, 100W with Poly Carb Globe Screw Release Grounded Reflector Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130103](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Hand Lamps](#)
Product Name Watertite
Taxonomy Lamps and Lights
Type Hand Lamps
UPC 78678829632

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 120.65mm (4.750")
Duty Wet Location
Guard Included Yes
Guard Type Grounded, Reflector, Screw Release
Height 457.20mm (18.000")
Length N/A
Material - Globe Clear Polycarbonate
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120V AC

Material Info

Engineering Number 1203RB163P



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130103 Series](#)