

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **130105-0028**  
**Status:** **Active**  
**Description:** Super-Safeway™ Rubber Hand Lamp 75W with LOVOLT® In-line Transformer Screw Release Guard, Cord Type 14/2 SOOW, 7.62m (25.0' ) Cord Length

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family	Portable Lighting
Series	<u>130105</u>
Depth	101.60mm (4.000")
Height	374.65mm (14.750")
Length	N/A
NEMA Configuration	NEMA 5-15
Outlet	None
Product Name	Super-Safeway™
Type	Specialty Light
UPC	78678862500
Woodhead	Yes

**Physical**

Cord Length - Primary	3.04m (10.0' )
Cord Length - Secondary	7.62m (25.0' )
Duty	Industrial
Guard Included	No
Guard Type	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	75W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

**Material Info**

Old Part Number 1600-12A



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
 130105Series