

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050036](#)
Status: **Active**
Overview: Specialty Lighting
Description: Watertite Wet Location 35W 12V Flood Light with In-line Transformer, Switch Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130105](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 4X
 Outlet None
 Overview [Specialty Lighting](#)
 Product Name Watertite
 Taxonomy Lamps and Lights
 Type Hand Lamps, Specialty Light
 UPC 78678861561

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary 15.24m (50.0')
 Depth N/A
 Duty Wet Location
 Guard Included Yes
 Guard Type Screw Release
 Height 127.00mm (5.000")
 Length 228.60mm (9.000")
 Material - Guard #10 Gauge Vinyl Coated Steel
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
 Cord Type - Primary 16/3 SOOW
 Cord Type - Secondary 14/2 SOOW
 Lamp Type PAR36
 Lamp Wattage - Maximum 35W
 Lumens 350
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1612S



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130105 Series](#)