

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0044](#)
Status: **Active**
Description: Watertite® Wet Location Incandescent Hand Lamp, 100W with LOVOLT® In-line Transformer Cast Aluminum Guard, Cord Type 14/2 SOOW, 15.24m Cord Length

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130105
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Product Name	Watertite®
Type	Specialty Light
Woodhead	Yes

Physical

Cord Length - Primary	3.04m
Cord Length - Secondary	15.24m
Depth	120.65mm
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	457.20mm
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Material Info

Old Part Number	1631-12B
UPC	78678862540



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130105Series](#)