

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0050](#)
Status: **Active**
Description: LOVOLT® 400W 120V/12V Workstation with 4 Receptacles 15A Breaker, 16/3 SOOW Cord Type, 1.83m Cord Length

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130105](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 3R
 Outlet 2 - 60W07 Non-NEMA Crow Foot
 Product Name Woodhead®
 Type Specialty Light
 Woodhead Yes

Physical

Cord Length - Primary 1.83m
 Cord Length - Secondary N/A
 Depth 80.01mm
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 206.25mm
 Length 285.75mm
 Material - Guard N/A
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type N/A
 Cord Type - Primary 16/3 SOOW
 Lamp Type N/A
 Lamp Wattage - Maximum 400W
 Lumens N/A
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ
 Voltage (Secondary) - Maximum 12V AC

Material Info

Old Part Number 1640-12
 UPC 78678862520



EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130105Series](#)