

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130106-0112](#)  
**Status:** **Active**  
**Description:** Super-Safeway™ Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0' ) Lead 5 Sockets, Overall Length 7.62m (50.0' )

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Portable Lighting
Series	130106
Depth	47.625mm (1.875")
Height	107.95mm (4.250")
Length	15.24m (50.0' )
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Product Name	Super-Safeway™
Type	String Lights
UPC	78678879893
Woodhead	Yes

**Physical**

Cord Length - Primary	1.52m (5.0' )
Cord Length - Secondary	1.52m (5.0' )
Duty	Industrial
Guard Included	No
Guard Type	N/A
Material - Guard	N/A
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded

**Electrical**

Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Old Part Number	323523
-----------------	--------



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC  
Not Reviewed**

**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

130106Series