

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301060115](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets with Guards, NEMA 5-15 Plug, Overall Length 15.24m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130106](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Name Super-Safeway
 Taxonomy Lamps and Lights
 Type String Lights
 UPC 78678879896

Physical

Cord Length - Primary 1.52m (5.0')
 Cord Length - Secondary 1.52m (5.0')
 Depth 47.625mm (1.875")
 Duty Industrial
 Guard Included Yes
 Guard Type Steel
 Height 107.95mm (4.250")
 Length 15.24m (50.0')
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Stringer
 Packaging Type Carton
 Socket Construction Rubber Molded

Electrical

Bulb Type Incandescent
 Cord Type - Primary 12/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 200W
 Lumens 2000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 323526



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130106 Series](#)