

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301080122](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway 13W Fluorescent Hand Lamp no Switch with Cord Ballast Location, Cord Type 18/3 SJTOOW, Cord Length 7.62m (25.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Portable Lighting
Series	<a href="#">130108</a>
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	<a href="#">Hand Lamps</a>
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678867136

**Physical**

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	38.10mm (1.500")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	66.04mm (2.600")
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTOOW
Lamp Type	PL13/41
Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Engineering Number	1083-3NS
--------------------	----------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130108 Series](#)