

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130108-0170](#)
Status: **Active**
Description: Watertite® Wet Location 13W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJOW, Cord Length 7.62m

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130108
Depth	69.85mm
Height	N/A
Length	444.50mm
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Product Name	Watertite®
Type	Wide Area Lamps
Woodhead	Yes

Physical

Cord Length - Primary	7.62m
Cord Length - Secondary	N/A
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	16/3 SJOW
Lamp Type	PL13/41
Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number 1913SA



image - Reference only

EU RoHS

Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130108Series](#)