

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080173](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Watertite Wet Location 13W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJTOOW, Cord Length 15.24m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130108](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 4X
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Name Watertite
 Taxonomy Lamps and Lights
 Type Wide Area Lamps
 UPC 78678829023

Physical

Cord Length - Primary 15.24m (50.0')
 Cord Length - Secondary N/A
 Depth 69.85mm (2.750")
 Duty Wet Location
 Guard Included No
 Guard Type N/A
 Height N/A
 Length 444.50mm (17.500")
 Material - Globe Butyrate
 Material - Guard Nitrile Rubber 80 Shore A
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Cord Type - Primary 16/3 SJTOOW
 Lamp Type PL13/41
 Lamp Wattage - Maximum 13W
 Lumens 900
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1913SB



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130108 Series](#)