

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090007](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 7.62m (25.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
 Series [130109](#)
 Exclude SD Check Yes
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Hand Lamps](#)
 Product Literature Order No 987650-8053
 Product Name Safeway
 Type Hand Lamps
 UPC 78678861601

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth N/A
 Duty General
 Guard Included Yes
 Guard Type Steel
 Height N/A
 Length N/A
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Hand Held
 Net Weight 1078.188/g
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SJTOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 402



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130109 Series](#)