

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090017](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow Nylon 100W Hand Lamp with Switch, Molded Grips and Hide Away Guard, Cord Type 18/3 SJTW, Cord Length 6.10m (20.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
 Series [130109](#)
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Hand Lamps](#)
 Product Name Pro-Yellow
 Taxonomy Lamps and Lights
 Type Hand Lamps
 UPC 78678850114

Physical

Cord Length - Primary 6.10m (20.0')
 Cord Length - Secondary N/A
 Depth N/A
 Duty General
 Guard Included Yes
 Guard Type Hide Away
 Height N/A
 Length N/A
 Material - Guard Polypropylene
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 18/3 SJTW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number WT3C-20



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130109 Series](#)