

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090027](#)

Status: **Active**

Overview: [Hand Lamps](#)

Description: Pro-Yellow Nylon 150W Incandescent Hand Lamp with Side Outlet and Switch, Grips Molded, Cord Type 16/3 SJTW, Cord Length 15.24m (50.0'), Easy Access Metal Guard

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family	Portable Lighting
Series	130109
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	Hand Lamps
Product Name	Pro-Yellow
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678850116

Physical

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	Yes
Guard Type	Steel
Height	N/A
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	1914.158/g
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SJTW
Lamp Type	A21
Lamp Wattage - Maximum	150W
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	WT6C-50
--------------------	---------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130109 Series](#)