

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301110031](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Safety Yellow Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead, 5 Sockets, Full Ground Ring, Overall Length 15.24m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
 Series [130111](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Name Safety Yellow
 Taxonomy Lamps and Lights
 Type String Lights
 UPC 78678840870

Physical

Cord Length - Primary 2.43m (8.0')
 Cord Length - Secondary 0.61m (2.0')
 Depth N/A
 Duty Commercial
 Guard Included No
 Guard Type N/A
 Height N/A
 Length 15.24m (50.0')
 Material - Guard N/A
 Mounting Style Stringer
 Packaging Type Carton
 Socket Construction Molded

Electrical

Bulb Type Incandescent
 Cord Type - Primary 12/3 SJTW
 Lamp Type A21
 Lamp Wattage - Maximum 200W
 Lumens 2000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 5003



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130111](#) Series