

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301120246](#)
Status: **Active**
Overview: [Lighting Accessories](#)
Description: Guard Only (LITE-A-SITE), Polypropylene

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130112
Exclude SD Check	Yes
NEMA Configuration	N/A
Outlet	None
Overview	Lighting Accessories
Product Literature Order No	987650-8055
Product Name	Woodhead
Type	Accessory
UPC	78678879982

Physical


Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	109.22mm (4.300")
Duty	Commercial
Guard Included	Yes
Guard Type	Polypropylene
Height	165.10mm (6.500")
Length	N/A
Material - Guard	Polypropylene
Net Weight	45.359/g
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	N/A
Lamp Type	A21
Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Material Info

Engineering Number	STR101
--------------------	--------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130112 Series](#)