

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301280140](#)  
**Status:** **Active**  
**Description:** Heavy Duty Stranded Cable, Type SOW-SOW-A, 16 AWG, 4 Conductors, 76.20m Length, Yellow

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">130128</a>
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
Taxonomy	Industrial Cable
UPC	78678879960

**Physical**

Cable Length	76.20m
Circuits (Loaded)	4
Color - Cable Jacket	Yellow
Insulation	EP Rubber
Net Weight	53.977/g
Outer Jacket Diameter	10.41mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	16
Wire/Cable Type	SOW, SOW-A

**Electrical**

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	SY16-4
--------------------	--------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130128 Series](#)