

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301350291](#)  
**Status:** **Active**  
**Overview:** [Outlet Boxes](#)  
**Description:** Super-Safeway Angled Outlet Box, F3 (3/4") Cord Grip Body, Including (2) NEMA 5-20 Duplex Receptacles, & Plug, 7.62m (25.0') Cord Length, 12/3 SOW Cord

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                    |                              |
|--------------------|------------------------------|
| Product Family     | Power Distribution           |
| Series             | <a href="#">130135</a>       |
| Enclosure Rating   | N/A                          |
| GFCI Reset         | N/A                          |
| Mounting Style     | Portable                     |
| Open Neutral Relay | N/A                          |
| Overview           | <a href="#">Outlet Boxes</a> |
| Product Name       | Super-Safeway                |
| Receptacle Type    | Duplex                       |
| Taxonomy           | Power Distribution           |
| Type               | Angled Outlet Box            |
| UPC                | 78678828889                  |

**Physical**

|                       |                 |
|-----------------------|-----------------|
| Cord Diameter         | 15.24mm (.600") |
| Cord Grip Body Size   | F3 3/4"         |
| Cord Length           | 7.62m (25.0')   |
| Feed-Thru             | No              |
| Flip Lid              | No              |
| Material - Housing    | Rubber          |
| Number of Receptacles | 2               |
| Packaging Type        | Carton          |

**Electrical**

|                               |           |
|-------------------------------|-----------|
| Cord Type                     | 12/3 SOW  |
| Current - Maximum per Contact | 20.0A     |
| GFCI                          | No        |
| Ground Continuity Monitor     | No        |
| NEMA Configuration            | NEMA 5-20 |
| Voltage - Maximum             | 250V      |

**Material Info**

|                    |          |
|--------------------|----------|
| Engineering Number | 3332A123 |
|--------------------|----------|



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130135 Series](#)