

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301360027](#)  
**Status:** **Active**  
**Overview:** [Outlet Boxes](#)  
**Description:** Super-Safeway Multi-Tap (3) NEMA 5-20 Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, NEMA 5-20 Plug

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Power Distribution  
 Series [130136](#)  
 Enclosure Rating N/A  
 GFCI Reset N/A  
 Mounting Style Portable  
 Open Neutral Relay N/A  
 Overview [Outlet Boxes](#)  
 Product Name Super-Safeway  
 Receptacle Type Triple  
 Taxonomy Power Distribution  
 Type Multi-Tap and Strip Cordset  
 UPC 78678875617

**Physical**

Cord Diameter 15.24mm (.600")  
 Cord Grip Body Size Double C-Clamp  
 Cord Length 7.62m (25.0')  
 Feed-Thru No  
 Flip Lid No  
 Material - Housing Rubber  
 Number of Receptacles 3  
 Packaging Type Carton

**Electrical**

Cord Type 12/3 SOOW  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Ground Continuity Monitor No  
 NEMA Configuration NEMA 5-20  
 Voltage - Maximum 120V

**Material Info**

Engineering Number 31565A123



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130136 Series](#)