

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360037](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap (3) NEMA 5-15 Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SJOW Cord, NEMA 5-15 Plug, In-line GFCI

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Power Distribution
 Series [130136](#)
 Enclosure Rating N/A
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Outlet Boxes](#)
 Product Name Super-Safeway
 Receptacle Type Triple
 Taxonomy Power Distribution
 Type Multi-Tap and Strip Cordset
 UPC 78678801252

Physical

Cord Diameter 9.65mm (.380")
 Cord Grip Body Size Double C-Clamp
 Cord Length 7.62m (25.0')
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 3
 Packaging Type Bag

Electrical

Cord Type 14/3 SJOW
 Current - Maximum per Contact 15.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 120V

Material Info

Engineering Number 31593A143IN



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130136 Series](#)