

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360054](#)
Status: **Active**
Overview:
Description: Super-Safeway Multi-Tap (3) Non-NEMA 20A/125V/250V Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 12/3 SOW Cord, Non-NEMA 20A/125V/250V Plug

Agency Certification

CSA LR6837

General

Product Family Power Distribution
 Series [130136](#)
 Enclosure Rating N/A
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview outlet_boxes
 Product Name Super-Safeway
 Receptacle Type Triple
 Taxonomy Power Distribution
 Type Multi-Tap and Strip Cordset
 UPC 78678875657

Physical

Cord Diameter 15.24mm (.600")
 Cord Grip Body Size Double C-Clamp
 Cord Length 7.62m (25.0')
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 20.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration Non-NEMA
 Voltage - Maximum 120V

Material Info

Engineering Number 32708A123

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130136](#) Series