

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370100](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 0.305m (1.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

**Agency Certification**

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E38085 |

**General**

|                    |                            |
|--------------------|----------------------------|
| Product Family     | Power Distribution         |
| Series             | <a href="#">130137</a>     |
| Enclosure Rating   | N/A                        |
| GFCI Reset         | N/A                        |
| Mounting Style     | Portable                   |
| Open Neutral Relay | N/A                        |
| Overview           | wet_location__watertite174 |
| Product Name       | Super-Safeway              |
| Receptacle Type    | Duplex                     |
| Taxonomy           | Power Distribution         |
| Type               | Multiple Outlet Box        |
| UPC                | 78678879620                |

**Physical**

|                       |                 |
|-----------------------|-----------------|
| Cord Diameter         | 13.59mm (.535") |
| Cord Grip Body Size   | Double C-Clamp  |
| Cord Length           | 0.305m (1.0')   |
| Feed-Thru             | No              |
| Flip Lid              | No              |
| Material - Housing    | Rubber          |
| Number of Receptacles | 2               |
| Packaging Type        | Carton          |

**Electrical**

|                               |           |
|-------------------------------|-----------|
| Cord Type                     | 14/3 SOOW |
| Current - Maximum per Contact | 15.0A     |
| GFCI                          | No        |
| Ground Continuity Monitor     | No        |
| NEMA Configuration            | NEMA 5-15 |
| Voltage - Maximum             | 125V      |

**Material Info**

|                    |            |
|--------------------|------------|
| Engineering Number | 3000-1E143 |
|--------------------|------------|

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

**China RoHS**

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**