

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370130](#)  
**Status:** **Active**  
**Overview:** Watertite Extreme Wet-Location Wiring Solutions  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family Power Distribution  
 Series [130137](#)  
 Enclosure Rating NEMA 4  
 GFCI Reset N/A  
 Mounting Style Portable  
 Open Neutral Relay N/A  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Super-Safeway  
 Receptacle Type Duplex  
 Taxonomy Power Distribution  
 Type Multiple Outlet Box  
 UPC 78678879664

**Physical**

Cord Diameter 13.59mm (.535")  
 Cord Grip Body Size F2 1/2"  
 Cord Length 15.24m (50.0')  
 Feed-Thru No  
 Flip Lid Yes  
 Material - Housing Rubber  
 Number of Receptacles 2  
 Packaging Type Carton

**Electrical**

Cord Type 14/3 SOOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Ground Continuity Monitor No  
 NEMA Configuration NEMA 5-15  
 Voltage - Maximum 125V

**Material Info**

Engineering Number 3005-1B143



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

**China RoHS**

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)