

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370132](#)
Status: **Active**
Overview: Watertite Extreme Wet-Location Wiring Solutions
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 0.305m (1.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating NEMA 4
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Super-Safeway
 Receptacle Type Duplex
 Taxonomy Power Distribution
 Type Multiple Outlet Box
 UPC 78678879662

Physical

Cord Diameter 13.59mm (.535")
 Cord Grip Body Size F2 1/2"
 Cord Length 0.305m (1.0')
 Feed-Thru No
 Flip Lid Yes
 Material - Housing Rubber
 Number of Receptacles 2
 Packaging Type Carton

Electrical

Cord Type 14/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 3005-1E143



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)