

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370213](#)
Status: **Active**
Overview: Watertite Extreme Wet-Location Wiring Solutions
Description: Super-Safeway Factory-Wired, 3-Phase Stringer Set, 2-Sided, One Box/Phase on 3.05m Center, Color-Coded NEMA 5-20 Receptacles, 12/5 SOW Cord

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

| | |
|--------------------|---|
| Product Family | Power Distribution |
| Series | 130137 |
| Enclosure Rating | N/A |
| GFCI Reset | N/A |
| Mounting Style | Portable |
| Open Neutral Relay | N/A |
| Overview | Watertite Extreme Wet-Location Wiring Solutions |
| Product Name | Super-Safeway |
| Receptacle Type | Duplex |
| Taxonomy | Power Distribution |
| Type | 3-Phase Stringer Set |
| UPC | 78678874563 |

Physical

| | |
|-----------------------|-----------------|
| Cord Diameter | 18.03mm (.710") |
| Cord Grip Body Size | F3 3/4" |
| Cord Length | 9.14m (30.0') |
| Feed-Thru | Yes |
| Flip Lid | No |
| Material - Housing | Rubber |
| Number of Receptacles | 12 |
| Packaging Type | Carton |

Electrical

| | |
|-------------------------------|-----------|
| Cord Type | 12/5 SOW |
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Ground Continuity Monitor | No |
| NEMA Configuration | NEMA 5-20 |
| Voltage - Maximum | 250V |

Material Info

Engineering Number 3095-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)