

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370214](#)  
**Status:** **Active**  
**Overview:** Watertite Extreme Wet-Location Wiring Solutions  
**Description:** Super-Safeway Factory-Wired, 3-Phase Stringer Set, 2-Sided, One Box/Phase on 3.05m Center, Color-Coded NEMA 5-20 Receptacles, 12/5 SOW Cord, L21-20 Plug

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Power Distribution  
 Series [130137](#)  
 Enclosure Rating N/A  
 GFCI Reset N/A  
 Mounting Style Portable  
 Open Neutral Relay N/A  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Super-Safeway  
 Receptacle Type Duplex  
 Taxonomy Power Distribution  
 Type 3-Phase Stringer Set  
 UPC 78678874569

**Physical**

Cord Diameter 18.03mm (.710")  
 Cord Grip Body Size F3 3/4"  
 Cord Length 9.14m (30.0')  
 Feed-Thru Yes  
 Flip Lid No  
 Material - Housing Rubber  
 Number of Receptacles 12  
 Packaging Type Carton

**Electrical**

Cord Type 12/5 SOW  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Ground Continuity Monitor No  
 NEMA Configuration NEMA 5-20  
 Voltage - Maximum 125V

**Material Info**

Engineering Number 3095-002



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)