

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370241](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** [Watertite GFCI Coverplate Module for FS/FD Boxes, Clear Silicone, 20A/125V](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E68122

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	<a href="#">Watertite Extreme Wet-Location Wiring Solutions</a>
Product Name	Watertite
Receptacle Type	N/A
Taxonomy	Power Distribution
Type	Multiple Outlet Box
UPC	78678809566

**Physical**

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	Silicone
Number of Receptacles	0
Packaging Type	Carton

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	125V

**Material Info**

Engineering Number 3362GF

**Reference - Drawing Numbers**

Sales Drawing 1301370241-000, SD-130137-002-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)