

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420019](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Connector with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V, Cord Grip Body Size F4

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130142](#)
 IP Rating N/A
 NEMA Configuration Non-NEMA Locking
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Name Super-Safeway
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678870591

Physical

Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade Yes
 Poles 4-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 208V

Material Info

Engineering Number 2709

Reference - Drawing Numbers

Sales Drawing 1301420019-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130142 Series](#)