

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430125](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Watertite Extreme Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-20 125V

**Agency Certification**

CSA	LR6837
UL	E38085

**General**

Product Family	Wiring Devices
Series	<a href="#">130143</a>
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Overview	wet_location__watertite174
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Cordset
UPC	78678871007

**Physical**

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Locking Blade	No
Net Weight	555.000/g
Poles	2-pole/3-wire

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

**Material Info**

Engineering Number	14W33B123
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	1301430121-000
---------------	----------------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143](#) Series