

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430135](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Cordset 14 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA 5-15, 125V, Inline GFCI

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Wiring Devices
 Series [130143](#)
 IP Rating IP67
 NEMA Configuration NEMA 5-15
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type Single
 Specialty N/A
 Taxonomy Wiring Devices
 Type Cordset
 UPC 78678871038

Physical

Cord Grip Body Size F2 1/2"
 Flange No
 Flip Lid No
 Gender Male-Female
 Length 7.62m (25.0')
 Locking Blade No
 Net Weight 77.000/g
 Poles 2-pole/3-wire

Electrical

Cord Type 14/3 SJOW
 Current - Maximum per Contact 15.0A
 GFCI Yes-In-line
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 14W47A143IN



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130143 Series](#)