

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430195](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA L5-15, 125V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Wiring Devices
 Series [130143](#)
 IP Rating IP67
 NEMA Configuration NEMA L5-15
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type Single
 Specialty N/A
 Taxonomy Wiring Devices
 Type Cordset
 UPC 78678879684

Physical

Cord Grip Body Size F2 1/2"
 Flange No
 Flip Lid No
 Gender Male-Female
 Length 30.48m (100.0')
 Locking Blade Yes
 Net Weight 7221.184/g
 Poles 2-pole/3-wire

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 24W47D143

Reference - Drawing Numbers

Sales Drawing 1301430187-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130143 Series](#)