

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430257](#)
Status: **Active**
Overview: Watertite Extreme Wet-Location Wiring Solutions
Description: Super-Safeway Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 15.24m (50.0'), NEMA L16-30, 3ø 480V

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Wiring Devices
 Series [130143](#)
 IP Rating N/A
 NEMA Configuration NEMA L16-30
 Overview Watertite Extreme Wet-Location Wiring Solutions
 Product Name Super-Safeway
 Receptacle Type N/A
 Specialty N/A
 Taxonomy Wiring Devices
 Type Cordset
 UPC 78678870635

Physical

Flange No
 Flip Lid No
 Gender Male-Female
 Length 15.24m (50.0')
 Locking Blade Yes
 Net Weight 254.000/kg
 Poles 3-pole/4-wire

Electrical

Cord Type 10/4 SOOW
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 3ø 480V

Material Info

Engineering Number 2876B104



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130143 Series](#)