

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430271](#)

Status: **Active**

Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)

Description: Watertite Extreme Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 15.24m (50.0'), NEMA L14-30, 125V/250V

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family	Wiring Devices
Series	130143
Comments	125V and 250V
IP Rating	IP67
NEMA Configuration	NEMA L14-30
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	N/A
Specialty	N/A
Taxonomy	Wiring Devices
Type	Cordset
UPC	78678871288

Physical

Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Locking Blade	Yes
Net Weight	355.000/kg
Poles	3-pole/4-wire

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V

Material Info

Engineering Number	28W74B104
--------------------	-----------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130143 Series](#)