

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460052](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: [Watertite Extreme Connector, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Silicone Husk](#)

Documents:

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family [Wiring Devices](#)
 Series [130146](#)
 IP Rating [IP69K](#)
 NEMA Configuration [NEMA 5-20](#)
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name [Watertite Extreme](#)
 Receptacle Type [Single](#)
 Specialty [N/A](#)
 Taxonomy [Wiring Devices](#)
 Type [Connector](#)
 UPC [78678871122](#)

Physical

Cord Grip Body Size [F2 1/2"](#)
 Flange [No](#)
 Flip Lid [No](#)
 Gender [Female](#)
 Length [N/A](#)
 Locking Blade [No](#)
 Net Weight [107.954/g](#)
 Poles [2-pole/3-wire](#)

Electrical

Cord Type [N/A](#)
 Current - Maximum per Contact [20.0A](#)
 GFCI [No](#)
 Lighted Connector [No](#)
 Voltage - Maximum [125V](#)

Material Info

Engineering Number [15W33](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130146 Series](#)