

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460069](#)

**Status:** **Active**

**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)

**Description:** Watertite Extreme Extra Hard Outdoor Connector, 2 Pole/3 Wire, NEMA 6-20, 250V, Cord Grip Body Size F2, Black, Silicone Husk

**Documents:**

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family Wiring Devices  
Series [130146](#)  
IP Rating IP69K  
NEMA Configuration NEMA 6-20  
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
Product Name Watertite Extreme  
Receptacle Type Single  
Specialty N/A  
Taxonomy Wiring Devices  
Type Connector  
UPC 78678875359

**Physical**

Cord Grip Body Size F2 1/2"  
Flange No  
Flip Lid No  
Gender Female  
Length N/A  
Locking Blade No  
Poles 2-pole/3-wire

**Electrical**

Cord Type N/A  
Current - Maximum per Contact 20.0A  
GFCI No  
Lighted Connector No  
Voltage - Maximum 250V

**Material Info**

Engineering Number 15W48BLK



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130146 Series](#)