

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460100](#)

Status: **Active**

Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)

Description: Watertite Extreme Extra Hard Outdoor Connector with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V, Cord Grip Body Size F2, Black, Silicone Husk

Documents:

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130146](#)
IP Rating IP69K
NEMA Configuration NEMA L5-15
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite Extreme
Receptacle Type Single
Specialty N/A
Taxonomy Wiring Devices
Type Connector
UPC 78678871187

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Female
Length N/A
Locking Blade Yes
Net Weight 193.230/g
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V

Material Info

Engineering Number 25W47BLK



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130146 Series](#)