

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460129](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V

Documents:

3D Model	Brochure (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

Agency Certification

CSA	LR6837
UL	E68122

General

Product Family	Wiring Devices
Series	130146
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Receptacle
UPC	78678871402

Physical

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Locking Blade	No
Net Weight	12.440/g
Poles	2-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Engineering Number	60W47
--------------------	-------

Reference - Drawing Numbers

Sales Drawing	1301460129-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130146 Series](#)