

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460145](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Receptacle Single Flip Coverplate with Locking Blade, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V

Documents:

3D Model	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

Agency Certification

UL E68122

General

Product Family	Wiring Devices
Series	130146
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Receptacle
UPC	78678871580

Physical

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	3-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	10.0A, 15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V

Material Info

Engineering Number 65W07

Reference - Drawing Numbers

Sales Drawing 1301460145-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130146 Series](#)