

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460149](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V

**Documents:**

<a href="#">3D Model</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">3D Model (PDF)</a>	

**Agency Certification**

CSA	LR6837
UL	E68122

**General**

Product Family	Wiring Devices
Series	<a href="#">130146</a>
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Overview	<a href="#">Watertite Extreme Wet-Location Wiring Solutions</a>
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Receptacle
UPC	78678871502

**Physical**

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Locking Blade	Yes
Net Weight	387.821/g
Poles	2-pole/3-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

**Material Info**

Engineering Number	65W47
--------------------	-------

**Reference - Drawing Numbers**

Sales Drawing	1301460149-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130146 Series](#)