

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460157](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Receptacle with Duplex Flip Coverplate, 2 Pole/2 Wire, NEMA-L2-20, 250V

Documents:

3D Model	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

Agency Certification

CSA LR6837

General

Product Family	Wiring Devices
Series	130146
IP Rating	IP67
NEMA Configuration	NEMA L2-20
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Receptacle
UPC	78678871459

Physical

Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	2-pole/2-wire

Electrical


Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

Material Info

Engineering Number 67W07DPLX

Reference - Drawing Numbers

Sales Drawing 1301460157-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130146 Series](#)