

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470121](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** [Watertite Extreme Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, Neman L23-30, 480V, 3ø, F4](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family [Wiring Devices](#)  
Series [130147](#)  
IP Rating [IP67](#)  
NEMA Configuration [NEMA L23-30](#)  
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
Product Name [Watertite Extreme](#)  
Receptacle Type [Single](#)  
Specialty [N/A](#)  
Taxonomy [Wiring Devices](#)  
Type [Connector](#)  
UPC [78678871421](#)

**Physical**

Cord Grip Body Size [F4 1"](#)  
Flange [No](#)  
Flip Lid [No](#)  
Gender [Female](#)  
Length [N/A](#)  
Locking Blade [Yes](#)  
Poles [4-pole/5-wire](#)

**Electrical**

Cord Type [N/A](#)  
Current - Maximum per Contact [30.0A](#)  
GFCI [No](#)  
Lighted Connector [No](#)  
Voltage - Maximum [3Ø 600V](#)

**Material Info**

Engineering Number [29W83MB](#)

**Reference - Drawing Numbers**

Sales Drawing [1301470121-000](#)



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130147](#) Series