

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470135](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Male Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, NEMA L22-20, 3Ø 480V

Documents:

3D Model	Brochure (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

General

Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	NEMA L22-20
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	N/A
Specialty	N/A
Taxonomy	Wiring Devices
Type	Inlet
UPC	78678871456

Physical

Flange	No
Flip Lid	Yes
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	4-pole/5-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3Ø 480V

Material Info

Engineering Number	66W82
--------------------	-------

Reference - Drawing Numbers

Sales Drawing	1301470135-000
---------------	----------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)