

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301540042](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Super-Safeway Standard Molded W Cordset, 12 Gauge, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-15, 250V

**General**

Product Family	Wiring Devices
Series	<a href="#">130154</a>
IP Rating	N/A
NEMA Configuration	NEMA 6-15
Overview	heavyduty_industrial_wiring_devices
Product Name	Super-Safeway
Receptacle Type	Triple
Specialty	N/A
Taxonomy	Wiring Devices
Type	Molded W Cordset
UPC	78678800626

**Physical**

Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Locking Blade	No
Poles	2-pole/3-wire

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

**Material Info**

Engineering Number	1449-W
--------------------	--------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130154](#) Series