

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130154-0044](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Devices](#)
Description: Watertite® Standard Molded Y Cordset, 2 Pole/3 Wire SOW Cordset, Cordset Length 0.91m, NEMA 5-20, 125V

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LL52750

General

Product Family	Wiring Devices
Series	130154
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Overview	Watertite® Wet-Location Wiring Devices
Product Name	Watertite®
Receptacle Type	Duplex
Specialty	N/A
Type	Molded Y Cordset
Woodhead	Yes

Physical

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	N/A
Length	0.91m
Locking Blade	No
Poles	2-pole/3-wire

Electrical

Cord Type	12/3 SOW
Current - Maximum per Contact	20A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Old Part Number	14W33-Y
UPC	78678800606



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series
[130154Series](#)