

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301540048](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V

**Documents:**

[Drawing \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LL52750  
 UL E38085

**General**

Product Family Wiring Devices  
 Series [130154](#)  
 IP Rating IP67  
 NEMA Configuration NEMA 5-15  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Watertite Extreme  
 Receptacle Type Duplex  
 Specialty N/A  
 Taxonomy Wiring Devices  
 Type Molded Y Cordset  
 UPC 78678801400

**Physical**

Cord Grip Body Size F2 1/2"  
 Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 0.91m (3.0')  
 Locking Blade No  
 Net Weight 1023.757/g  
 Poles 2-pole/3-wire

**Electrical**

Cord Type 12/3 SOOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V

**Material Info**

Engineering Number 14W47-Y

**Reference - Drawing Numbers**

Sales Drawing 1301540048-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[130154 Series](#)