

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130154-0056](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway® Standard Molded Y Cordset, 2 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m, NEMA L5-15, 125V

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Wiring Devices
Series	130154
IP Rating	N/A
NEMA Configuration	NEMA L5-15
Overview	Heavy-Duty Industrial Wiring Devices
Product Name	Super-Safeway™
Receptacle Type	Duplex
Specialty	N/A
Type	Molded Y Cordset
Woodhead	Yes

Physical

Cord Grip Body Size	N/A
Flange	No
Flip Lid	No
Gender	N/A
Length	0.91m
Locking Blade	Yes
Poles	2-pole/3-wire

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	15A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Old Part Number	2447-Y
UPC	78678800616



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130154Series](#)