

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301540059](#)

Status: **Active**

Overview:

Description: Watertite Extreme Inline GFCI Molded W Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA L5-15, 125V

General

Product Family	Wiring Devices
Series	130154
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Overview	wet_location__watertite174
Product Name	Watertite Extreme
Receptacle Type	Triple
Specialty	N/A
Taxonomy	Wiring Devices
Type	Molded W Cordset
UPC	78678835637

Physical

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Locking Blade	Yes
Poles	2-pole/3-wire

Electrical

Cord Type	12/3 SJOW
Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Engineering Number	24W47-W-IN
--------------------	------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130154](#) Series